

BALL BEARING GUIDE POST SETS

—MOVABLE STOPPER—



Printed in Red

The volume discount rate is also applicable to alteration cost.
All price & lead time are to be quoted.

RoHS

MYA (Aluminum ball cage type) **MYAP** (With dowel holes / Aluminum ball cage type)

RoHS

MYJ (Resin type) **MYJP** (With dowel holes / Resin type)

⚠ Perpendicularity between the die holder's bottom and the guide post : Less than 0.02 against 100.

D	D ₁	A	B	a	b	d	H	H ₁	T	L _s	M	ℓ	a ₁	b ₁	eH ₇	⑥ Attached bolts	⑦ Attached dowel pin	
20	26	74	44	56	30	6.6	30	50	15	50	0~20	56	28	15	6	+0.012	CB 6-30	MSTM 6-20
25	31	84	48	66	30	9	30	50	20	50	0~20	66	33	15	8	+0.015	CB 8-35	MSTM 8-30
32	40	100	58	76	36	11	40	60	20	60	0~25	76	38	18	8	0	CB10-40	MSTM 8-30
38	48	130	75	100	44	11	50	70	25	70	0~29	100	50	22	10		CB10-45	MSTM10-40
50	60	155	90	125	60	14	65	90	25	90	0~42	125	62.5	30	10		CB12-50	MSTM10-40

Catalog No. Type	D	L	U/Price Q'ty : 1~9			
			MYA	MYAP	MYJ	MYJP
MYA MYAP MYJ MYJP*	20*	90* 100* 110* 120*				
		130* 140* 150* 160				
	25*	90* 100* 110* 120*				
		130* 140* 150* 160*				
		170* 180* 200*				
32*	110* 120* 130* 140* 150*					
	160* 170* 180* 200*					
	220* 240* 260*					
38*	130* 140* 150* 160*					
	170* 180* 200* 220					
	240* 260 300*					
50	170 180 200					
	220 240 260					
	300 350					

Quotation

MYJP with * are Stock Product.

Order Catalog No. — L **Volume discount rate**

MYJ 25 — 90

Quantity	1~9	10~19	20~29	30~50
Rate	—	5%	10%	15%

Delivery SGP Stock 3 Days 5 Days Express T Express A

⚠ For area out of Singapore please refer to P.i.

Alteration Catalog No. — L(LC) — (M·B·H·N·C...etc.)

MYAP 50 — LC230 — B-H

5 Days Express T Express A

⚠ For area out of Singapore please refer to P.i.

Alterations	Code	Spec.	D	Price
	LC	Changes post length 1mm increments LCmin ≤ LC < Lmax	20·25·32 38·50	Quotation
	Holder M	Machines tap holes for mounting stroke end block. ⊗ D20 : Not available	25~50	Free of Change
	Bushing B	Machines flange plane. Reversed type allows lowering the die height.	20·25·32	Quotation
	Holder H	⚠ Combination with alterations W and M available. ⚠ The post length is measured from the holder's bottom.	38·50	Quotation

Alterations	Code	Spec.	D	Price																								
	BKC	Changes bushing height tolerance H1±0.2 ⇨ ±0.1	25·32 38·50	Quotation																								
	HKC	Changes holder height tolerance H±0.2 ⇨ ±0.1	25·32 38·50																									
	N	Machines 2 positioning dowel holes on the holder. ⚠ Applicable to MYA and MYJ. ⚠ Dowel pins are not attached.	20·25·32 38·50	Quotation																								
	C	Machines 1 positioning dowel hole at the center of the post. ⚠ Dowel pins are not attached.	20·25·32 38·50																									
	BSC	Attached Ball bearing cage will be changed to high rigidity type. Aluminum : MBS → MBSH Resin : MBJ → MBJH		Price																								
				<table border="1"> <tr> <th>D</th> <th>Material</th> <th>MBSH</th> <th>MBJH</th> </tr> <tr> <td>20</td> <td>Aluminum</td> <td>50</td> <td>50</td> </tr> <tr> <td>25</td> <td>Aluminum</td> <td>50</td> <td>50</td> </tr> <tr> <td>32</td> <td>Aluminum</td> <td>60</td> <td>60</td> </tr> <tr> <td>38</td> <td>Aluminum</td> <td>70</td> <td>70</td> </tr> <tr> <td>50</td> <td>Aluminum</td> <td>90</td> <td>90</td> </tr> </table>	D	Material	MBSH	MBJH	20	Aluminum	50	50	25	Aluminum	50	50	32	Aluminum	60	60	38	Aluminum	70	70	50	Aluminum	90	90
D	Material	MBSH	MBJH																									
20	Aluminum	50	50																									
25	Aluminum	50	50																									
32	Aluminum	60	60																									
38	Aluminum	70	70																									
50	Aluminum	90	90																									

Stocks Availability Subjected to Prior Sales.