

High Speed Steel  
SKH51  
4mm head



# STRAIGHT EJECTOR PINS

— STANDARD —



SGP Stock

Printed in Red



H	T	Catalog No.	P	L Selection
2		0.2		60
		0.3		60
3		0.4 0.5		60 100
		0.6 0.7		100 150
		0.8 0.9		100 150
		1 1.1 1.2 1.3 1.4		100 150 200
		1.5		100 150 200 250
4		1.6		100 150 200 250
		1.7 1.8 1.9		100 150 200
		2		100 150 200 250 300
		2.1		100 150 200 250
		2.2 2.3 2.4		100 150 200
5		2.5		100 150 200 250 300
		2.6		100 150 200 250
		2.7 2.8 2.9		100 150 200
		3		100 150 200 250 300 350
		3.1		100 150 200 250
7		3.2 3.3 3.4		100 150 200
		3.5		100 150 200 250 300 350
		3.6		100 150 200 250
		3.7 3.8 3.9		100 150 200
		4		100 150 200 250 300 350
8		4.1		100 150 200 250
		*4.2 *4.3 *4.4		100 150 200
		4.5		100 150 200 250 300 350
		4.6		100 150 200 250
		*4.7 *4.8 *4.9		100 150 200
9		5		100 150 200 250 300 350
		5.1		100 150 200 250
		5.5		100 150 200 250 300 350
		5.6		100 150 200 250
		6		100 150 200 250 300 350
10		6.1		100 150 200 250
		6.5		100 150 200 250 300 350
		6.6		100 150 200 250
		7		100 150 200 250 300 350
		7.1		100 150 200 250
11		*7.5 *7.6		100 150 200 250
		8		100 150 200 250 300 350
		8.1		100 150 200 250
		*8.5 *8.6		100 150 200 250
		9		100 150 200 250 300 350
15		*9.1 *9.5 *9.6		100 150 200 250
		10		100 150 200 250 300 350
		10.1		100 150 200 250
		*10.5 *10.6 *11 *11.1		100 150 200 250
		*11.5 *11.6		100 150 200 250
17		12		150 200 250 300 350

EPH (P<sub>-0.005</sub>)

EPHE-B (P<sub>-0.02</sub>)

When \* is indicated for P dimension, production time is 3 business days. Please take the order for head JIS type [EPHJ] (P<sub>-0.005</sub>) / [EPHJE] (P<sub>-0.01</sub>).

The quantity discount rate is also applicable to alteration cost. All price & lead time are to be quoted.

Order Catalog No. EPH 1.5 L 150 Delivery SGP Stock 3 Days

Alterations Catalog No. EPH 2.5 L 150 TC3.0 5 Days Express T A

P dimension with \* mark  
5 Days Express T A  
For area out of Singapore please refer to P.i.  
Express services not available for NHC · NHN

Alterations	Code	Spec.	Price
	VKC	Precision single flat cutting P/2 ≤ VKC < H/2	Quotation
	VWC	Precision two flats cutting P/2 ≤ VWC < H/2	
	KC	Single flat cutting P/2 ≤ KC < H/2	
	WKC	Two flats cutting P/2 ≤ WKC < H/2	
	KAC KBC	Varied width parallel flats cutting P/2 ≤ KAC < H/2 KBC=0.1mm increments only KAC < KBC < H/2	
	RKC	Two flats (right angled) cutting P/2 ≤ RKC < H/2	
	DKC	Three flats cutting P/2 ≤ DKC < H/2	
	SKC	Four flats cutting P/2 ≤ SKC < H/2	
	KGC	Two flats (angled) cutting P/2 ≤ KGC < H/2 AG=1° increments 0 < AG < 360	
	KTC	Three flats cutting at 120° P/2 ≤ KTC < H/2	

Unit of designation 0.05mm increments possible

Unit of designation 0.1mm

(1) To align the key flat with the shaft diameter

(2) To designate arbitrary key flat dimensions

Quantity discount rate

Quantity	Rate
1~49	5%
50~100	5%

Catalog No.	U/Price for 1~49
Type	
P	
L60	L100
L150	L200
L250	L300
L350	

EPH EPHE-B

Quotation

Alterations	Code	Spec.	Price
	HC	HC=0.1mm increments P+1 ≤ HC < H, P ≥ 1.5	Quotation
	HCC	HCC=0.1mm increments P+1 ≤ HCC < H-0.3, P ≥ 1.5	
	TC	TC=0.1mm increments 2.0 ≤ TC < 4, P ≥ 1.5 Dimension L becomes shorter by (4-TC)	
	NC	Dowel hole boring Available when H ≥ 4 Combination with other than NHC · NHN not available.	
	NCW	Dowel hole boring + Spring pin driving Available when H ≥ 4 Combination with other than NHC · NHN not available.	
	NCS	Dowel hole boring + Dowel pin driving Available when H ≥ 4 Combination with other than NHC · NHN not available.	
	NHC	Numbering on the head Available when H ≥ 2 Combination with SKC not available.	
	NHN	Automatic sequential numbering on the head Available when H ≥ 2 Combination with SKC not available.	

Catalog No.	U/Price for 1~49
Type	
P	
L100	L150
L200	L250
L300	L350

EPH EPHE-B

Quotation

Stocks Availability Subjected to Prior Sales.